



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400287-31M League

League Collection Four-Light Matte Black and Etched Glass Modern Farmhouse Chandelier Light

Category: Island/Linear
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Length: 39-3/4 in
 Depth: 14 in
 Height: 14-1/2 in
 Overall Ht. W/Chain Or Stem: 77-1/2 in

Etched Glass Cylindrical
 Width: 4-1/8 in
 Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	90 in of wire supplied	Quantity: four 100 W max. A19 or LED equivalent	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	E26 base Porcelain Socket	1-year Limited Warranty
Two pieces of 48 in of 9 Gauge chain supplied (2) with quick links		Fully dimmable with dimmable bulbs	
two 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 1.37" W, 0.75" ht., 4.75" depth			