

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400291-31M
Canebrake

Canebrake Collection Five-Light Matte Black Farmhouse Chandelier Light

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Construction



Length: 30-1/8 in
Diameter: 30-1/8 in
Height: 18 in
Overall Ht. W/Chain: 93 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(5) Candelabra Base (E12) Lamp Type	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
6 feet of 9 gauge chain supplied (1) with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			