

Project:			
Fixture Type:			
Location:			
Contact:			

P400292-31M

Canebrake

Canebrake Collection Six-Light Matte Black Farmhouse Chandelier Light

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction



Length: 40 in Diameter: 40 in Height: 24 in

Overall Ht. W/Chain: 99 in

		, , , , , , , , , , , , , , , , , , , ,	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(6) Candelabra Base (E12) Lamp Type	cETLus Dry Location Listed
1/8 IP mounting plate for outlet 120 VAC box included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
6 feet of 9 gauge chain supplied		·	
(1) with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			