

Project:		
Fixture Type:		
Location:		
Contact:		

P400298-009 Saffert

Saffert Collection Three-Light New Traditional Brushed Nickel Clear Glass Linear Island Chandelier Light

Category: Island/Linear Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bowl



Width: 40 in Depth: 7-9/16 in Height: 11-7/8 in

Overall Ht. W/Stem: 67-1/2 in

Clear Glass Bowl Width: 7-1/2 in Height: 6-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	15 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Two 6", eight 12" lengths of stem		socket	
included		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 18.18" W., 0.75" ht., 6" depth	Fully dimmable with dimmable bulbs		