PROGRESS LIGHTING

Project:		
Fixture Type:		

Location: Contact:

P400300-009 Parkhurst

Parkhurst Collection Six-Light New Traditional Brushed Nickel Linear Island Chandelier Light

Category: Island/Linear Finish: Brushed Nickel (Plated) Construction: Steel Construction



Width: 42 in Depth: 13 in Height: 15-1/8 in Overall Ht. W/Chain Or Stem: 89-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Two pieces of 48 in of 9 Gauge		socket	
chain supplied (2) with quick links		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Two 12" lengths of stem included		bulbs	

Canopy covers a standard 4" recessed outlet box: 18.12" W., 0.75" ht., 4.5" depth