

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400300-109 Parkhurst

Parkhurst Collection Six-Light New Traditional Brushed Bronze Linear Island Chandelier Light

Category: Island/Linear
Finish: Brushed Bronze (Plated)
Construction: Steel Construction



Width: 42 in
Depth: 13 in
Height: 15-1/8 in
Overall Ht. W/Chain Or Stem: 89-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Two pieces of 48 in of 9 Gauge chain supplied (2) with quick links		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Two 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 18.12" W., 0.75" ht., 4.5" depth			