PROGRESS LIGHTING[™]

Project:

Fixture Type:

Location:

Contact:

P400302-009 Galloway

Category: Chandeliers Finish: Brushed Nickel (Plated) with Grey Washed Oak accent Construction: Steel Construction



Diameter: 30 in Height: 28-1/4 in Overall Ht. W/Chain: 103 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied with quick link		socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.816" ht., 5.12" depth		Fully dimmable with dimmable bulbs	