## PROGRESS LIGHTING<sup>™</sup>

Project:		
Fixture Type:		
Location:		

Contact:

## P400302-31M Galloway

Category: Chandeliers Finish: Matte Black (Painted) with Distressed White accent Construction: Steel Construction



Diameter: 30 in Height: 28-1/4 in Overall Ht. W/Chain: 103 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
6 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.816" ht., 5.12" depth		Fully dimmable with dimmable bulbs	