

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400307-109 Haas

Haas Collection Four-Light Brushed Bronze Mid-Century Modern Chandelier

**Category:** Chandeliers

**Finish:** Brushed Bronze (Painted)

**Construction:** Steel Construction

**Glass/Shade:** Etched Opal Glass Round



Length: 26-1/4 in  
Width: 16-1/2 in  
Height: 12 in  
Overall Ht. W/Stem: 62-1/2 in

Etched Opal Glass Round  
Width: 6 in  
Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	