

| Project:      |  |  |  |
|---------------|--|--|--|
| Fixture Type: |  |  |  |
| Location:     |  |  |  |
| Contact:      |  |  |  |

## P400308-009

## Haas

Haas Collection Six-Light Brushed Nickel Mid-Century Modern Chandelier

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Round



Diameter: 33-1/2 in Height: 12-1/2 in

Overall Ht. W/Stem: 62-1/2 in

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

| MOUNTING  | ELECTRICAL               | LAMPING  | ADDITIONAL INFORMATION    |
|---|--------------------------|--|---------------------------|
| Ceiling Stem  | 10 feet of wire supplied | (6) Candelabra Base (E12) Socket   | cULus Dry Location Listed |
| Mounting plate for outlet box included  | 120 VAC                  | Lamp Type G16.5  | 1-year Limited Warranty   |
| One 6", four 12" lengths of stem included   |                          | Incandescent: 60-watt MAX per<br>socket<br>LED: 12.5-watt MAX per socket |                           |
| Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth |                          | Fully dimmable with dimmable bulbs                                       |                           |