

Project:
Fixture Type:
Location:
Contact:

## P400308-109

Haas Collection Six-Light Brushed Bronze Mid-Century Modern Chandelier

Category: Chandeliers

Finish: Brushed Bronze (Painted)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Round



Diameter: 33-1/2 in Height: 12-1/2 in

Overall Ht. W/Stem: 62-1/2 in

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	