


Project:		
Fixture Type:		
Location:		
Contact:		

P400308-31M

Haas

Haas Collection Six-Light Matte Black Mid-Century Modern Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Etched Opal Glass Round



Diameter: 33-1/2 in Height: 12-1/2 in

Overall Ht. W/Stem: 62-1/2 in

Etched Opal Glass Round

Width: 6 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
One 6", four 12" lengths of stem	socket		
included	LED: 12.5-watt MAX per socket		
Canopy covers a standard 4" recessed outlet box: 5.12" W.,	Fully dimmable with dimmable bulbs		
0.87" ht., 5.12" depth			