

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400309-31M Trimble

Trimble Collection Three-Light Matte Black Chandelier

Category: Chandelier
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Metal Metal Cone



Diameter: 44-1/8 in
Height: 11-1/8 in
Overall Ht. W/Chain And Stem: 77 in

Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	15 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Six links of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 5.81" W., 1.12" ht., 5.81" depth			