

Project:		
Fixture Type:		
Location:		
Contact:		

## P400312-31M

## **Burgess**

Burgess Collection Four-Light Matte Black Modern Farmhouse Island Light

Category: Island/Linear Finish: Matte Black (Painted) Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical



Length: 42 in Width: 9-3/8 in Height: 11-1/4 in

Overall Ht. W/Chain And Stem: 77 in

Clear Seeded Glass Cylindrical

Width: 4-5/16 in Height: 6-5/8 in

		rieight. o jjo m	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	15 feet of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type A19	1-year Limited Warranty
1/8 IP mounting plate for outlet			
box included		Incandescent: 60-watt MAX per socket	
Two pieces of Six links of 9 Gauge chain supplied (2) with		LED: 12.5-watt MAX per socket	
quick links		Fully dimmable with dimmable bulbs	
Two 6", eight 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 12.18" W., 1" ht., 4.75" depth			