

Project:			
Fixture Type:			
Location:			
Contact:			

P400313-009

Gilliam

Gilliam Collection Six-Light Brushed Nickel New Traditional Chandelier

Category: Chandeliers Finish: Brushed Nickel (Plated) Construction: Steel Construction



Diameter: 27-5/8 in Height: 24-7/8 in Overall Ht. W/Chain: 88 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.81" ht., 5" depth		Fully dimmable with dimmable bulbs	