

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400313-31M

### Gilliam

Gilliam Collection Six-Light Matte Black New Traditional Chandelier

**Category:** Chandeliers  
**Finish:** Matte Black (Painted)  
**Construction:** Steel Construction



Diameter: 27-5/8 in  
Height: 24-7/8 in  
Overall Ht. W/Chain: 88 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.81" ht., 5" depth		Fully dimmable with dimmable bulbs	