

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P400314-009**  
**Gilliam**

Gilliam Collection Nine-Light Brushed Nickel New Traditional Chandelier

**Category:** Chandeliers  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction



Diameter: 35-1/2 in  
Height: 26-1/2 in  
Overall Ht. W/Chain: 89-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(9) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.81" ht., 5" depth		Fully dimmable with dimmable bulbs	