

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400315-163
Gilliam

Gilliam Collection Fifteen-Light Vintage Brass New Traditional Chandelier

Category: Chandeliers
Finish: Vintage Brass (Plated)
Construction: Steel Construction



Diameter: 35-1/2 in
Height: 38-3/8 in
Overall Ht. W/Chain: 101-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	6 feet of wire supplied	(15) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/4 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.81" ht., 5" depth		Fully dimmable with dimmable bulbs	