## PROGRESS LIGHTING<sup>™</sup>

Project:		
Fixture Type:		
Location:		

Contact:

## P400316-31M Goodwin

Goodwin Collection Five-Light Matte Black Modern Farmhouse Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Diameter: 24 in Height: 15-1/2 in Overall Ht. W/Chain: 66-1/2 in

Clear Glass Cylindrical Width: 3-1/2 in Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(5) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	