PROGRESS LIGHTING

Project:		
Fixture Type:		
Location:		

Contact:

P400317-009 Goodwin

Goodwin Collection Four-Light Brushed Nickel Modern Farmhouse Island Light

Category: Island/Linear Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 40-3/8 in Width: 4-3/8 in Height: 16-3/4 in Overall Ht. W/Chain: 68-1/2 in

Clear Glass Cylindrical Width: 4-5/16 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	96 in of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Two pieces of 48 in of 9 Gauge		Incandescent: 60-watt MAX per socket	
chain supplied (2) with quick links		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 14.12" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs	