PROGRESS LIGHTING

| Project: | | |
|---------------|--|--|
| Fixture Type: | | |
| Location: | | |

Contact:

P400317-31M Goodwin

Goodwin Collection Four-Light Matte Black Modern Farmhouse Island Light

Category: Island/Linear Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Length: 40-3/8 in Width: 4-3/8 in Height: 16-3/4 in Overall Ht. W/Chain: 68-1/2 in

Clear Glass Cylindrical Width: 4-5/16 in Height: 6 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|------------------------|---|---------------------------|
| Ceiling Chain | 96 in of wire supplied | (4) Medium Base (E26) Socket | cULus Dry Location Listed |
| 1/8 IP mounting plate for outlet box included | 120 VAC | Lamp Type A19 | 1-year Limited Warranty |
| Two pieces of 48 in of 9 Gauge | | Incandescent: 60-watt MAX per socket | |
| chain supplied (2) with quick links | | LED: 12.5-watt MAX per socket | |
| Canopy covers a standard 4" recessed outlet box: 14.12" W., 0.75" ht., 4.5" depth | | Fully dimmable with dimmable bulbs | |