

Project:		
Fixture Type:		
Location:		

Contact:

P400318-31M

Breckenridge

Breckenridge Collection Five-Light Matte Black Rustic Farmhouse Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Construction



Diameter: 26 in Height: 21 in

Overall Ht. W/Chain: 96 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Chain	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cETLus Dry Location Listed	
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty	
6 feet of 9 Gauge chain supplied	Incandescent: 60-watt MAX per socket			
with quick link	LED: 12.5-watt MAX per socket			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth	Fully dimmable with dimmable bulbs			