

Project:

Fixture Type:

Location:

Contact:

P400321-31M Laramie

Laramie Collection Three-Light Matte Black Rustic Modern Clear Seeded Glass Chandelier

Category: Chandeliers

Finish: Matte Black (Painted) with Gray Sisal accent

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical,



Diameter: 18-1/8 in Height: 14 in

Overall Ht. W/Stem And Swivel: 70.5 in

Clear Seeded Glass Cylindrical

Width: 4 in Height: 6-1/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|---|--------------------------|---|---------------------------|
| Ceiling Stem | 10 feet of wire supplied | (3) Medium Base (E26) Socket | cULus Dry Location Listed |
| Mounting plate for outlet box included | 120 VAC | Lamp Type A19 Incandescent: 60-watt MAX per | 1-year Limited Warranty |
| One 6", four 12" lengths of stem included | | socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs | |
| Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth | | | |