

Project:

Fixture Type:

Location:

Contact:

## P400322-31M Laramie

Laramie Collection Four-Light Matte Black Rustic Modern Clear Seeded Glass Chandelier

Category: Chandeliers

Finish: Matte Black (Painted) with Gray Sisal accent

Construction: Steel Construction

Glass/Shade: Clear Seeded Glass Cylindrical,



Diameter: 24 in Height: 14 in

Overall Ht. W/Stem And Swivel: 70.5 in

Clear Seeded Glass Cylindrical

Width: 4 in Height: 6-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		Fully dimmable with dimmable bulbs	