

Project:		
Fixture Type:		
Location:		
Contact:		

P400323-163

Laila

Laila Collection Four-Light Vintage Brass Coastal Chandelier with Woven Jute Accents

Category: Chandeliers

Finish: Vintage Brass (Plated) with Jute accent

Construction: Steel Construction



Diameter: 22-3/8 in Height: 23-5/8 in Overall Ht. W/Chain: 98-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
6 feet of 9 Gauge chain supplied		socket	
with quick link		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 5.12" W.,		bulbs	
0.81" ht., 5.12" depth			