

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400325-109

Atwell

Atwell Collection Five-Light Brushed Bronze Mid-Century Modern Chandelier

Category: Chandeliers
Finish: Brushed Bronze (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Round



Diameter: 28 in
 Height: 5-7/8 in
 Overall Ht. W/Stem: 61-1/2 in

Clear Glass Round
 Width: 5-7/8 in
 Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	