

Project:			
Fixture Type:			
Location:			
Contact:			

## P400326-109

## **Atwell**

 $\label{thm:light-bound} At well \ Collection \ Four-Light \ Brushed \ Bronze \ Mid-Century \ Modern \ Island \ Light$ 

Category: Island/Linear Finish: Brushed Bronze (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Round



Length: 40 in Width: 14-3/4 in Height: 5-7/8 in

Overall Ht. W/Stem: 61-1/2 in

Clear Glass Round Width: 5-7/8 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type G16.5	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth		Fully dimmable with dimmable bulbs	