

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400337-109 Trimble

Trimble Collection Four-Light Brushed Bronze Linear Chandelier

Category: Chandeliers

Finish: Brushed Bronze (Plated) with Matte Black accent

Construction: Steel Construction



Diameter: 22-3/8 in (does not include bulbs)

Height: 7 in

Overall Ht. W/Stem And Swivel: 62 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.87" ht., 5.12" depth		Fully dimmable with dimmable bulbs	