

Project: \_\_\_\_\_  
 Fixture Type: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Contact: \_\_\_\_\_

## P400338-191 Arya

Arya Collection Eight-Light Brushed Gold Luxe Linear Chandelier

**Category:** Island/Linear  
**Finish:** Brushed Gold (Plated)  
**Construction:** Steel Construction



Width: 40 in  
 Depth: 13 in  
 Height: 10-3/4 in (does not include bulbs)  
 Overall Ht. W/Stem And Swivel: 63 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	6 feet of wire supplied	(8) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 40-watt MAX per socket LED: 10-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	