

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400338-31M Arya

Arya Collection Eight-Light Matte Black Luxe Linear Chandelier

Category: Island/Linear

Finish: Matte Black (Painted)

Construction: Steel Construction



Width: 40 in
Depth: 13 in
Height: 10-3/4 in (does not include bulbs)
Overall Ht. W/Stem And Swivel: 63 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	6 feet of wire supplied	(8) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 40-watt MAX per socket LED: 10-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	