

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400339-191 Arya

Arya Collection Twelve-Light Brushed Gold Luxe Chandelier

Category: Chandeliers
Finish: Brushed Gold (Plated)
Construction: Steel Construction



Diameter: 24-1/8 in
 Height: 10-3/4 in (does not include bulbs)
 Overall Ht. W/Stem And Swivel: 63 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	6 feet of wire supplied	(12) Candelabra Base (E12) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
One 6", four 12" lengths of stem included		Incandescent: 40-watt MAX per socket LED: 10-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.87" W., 0.75" ht., 4.87" depth		Fully dimmable with dimmable bulbs	