

Project:			
Fixture Type:			
Location:			
Contact:			

P400342-009

Vertex

Vertex Collection Three-Light Brushed Nickel Etched White Contemporary Convertible Chandelier

Category: Chandeliers **Finish:** Brushed Nickel (Plated)

Construction: Steel Construction
Glass/Shade: Etched White Glass Cone



Diameter: 18 in Height: 16-3/4 in

Overall Ht. W/Chain: 68 in

Etched White Glass Cone

Width: 4-3/4 in Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	10 feet of wire supplied	(3) Medium Base (E26) Socket	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth		Fully dimmable with dimmable bulbs	