



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____



P400349-009 Adley

Adley Collection Three-Light Brushed Nickel Etched White Opal Glass New Traditional Semi-Flush Convertible Light

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched White Glass Bell

Diameter: 18-1/8 in
 Height: 16-1/8 in
 Overall Ht. W/Chain: 68 in

Etched White Glass Bell
 Width: 4 in
 Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	10 feet of wire supplied	(3) Medium Base (E26) Porcelain	cULus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth		Fully dimmable with dimmable bulbs	