

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400350-009
Adley

Adley Collection Five-Light Brushed Nickel Etched White Opal Glass New Traditional Chandelier

Category: Chandeliers
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched White Glass Bell



Diameter: 22-7/8 in
Height: 17-1/4 in
Overall Ht. W/Chain: 69 in

Etched White Glass Bell
Width: 4 in
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	10 feet of wire supplied	(5) Medium Base (E26) Porcelain	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
48 in of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth		Fully dimmable with dimmable bulbs	