

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400351-31M
Adley

Adley Collection Nine-Light Matte Black Etched White Glass New Traditional Chandelier

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched White Glass Bell



Diameter: 28 in
Height: 26-1/8 in
Overall Ht. W/Chain: 90 in

Etched White Glass Bell
Width: 4 in
Height: 5-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	15 feet of wire supplied	(9) Medium Base (E26) Porcelain	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
5 feet of 9 Gauge chain supplied with quick link		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.75" ht., 5" depth		Fully dimmable with dimmable bulbs	