

Project:			
Fixture Type:			
Location:			
Contact:			

P400354-31M

Rivera

Rivera Collection Four-Light Matte Black Luxe Industrial Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Housing

Glass/Shade: Clear textured Glass Flat Square/Rectangular



Diameter: 20-1/2 in Height: 22-1/2 in

Overall Ht. W/Chain And Stem: 84-1/2 in

Clear textured Glass Flat Square/Rectangular

Width: 9-5/8 in Height: 5-1/2 in

	1108110.) 1/2 111			
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(4) Medium Base (E26) Socket	cULus Dry Location Listed	
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty	
3 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.		
One 6", four 12" lengths of stem included				
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth				