

Project:		
Fixture Type:		
Location:		
Contact:		

P400355-31M

Rivera

Rivera Collection Six-Light Matte Black Luxe Industrial Chandelier

Category: Chandeliers Finish: Matte Black (Painted) Construction: Steel Housing

Glass/Shade: Clear textured Glass Flat Square/Rectangular



Diameter: 30 in Height: 24 in

Overall Ht. W/Chain And Stem: 86 in

Clear textured Glass Flat Square/Rectangular

Width: 10-7/8 in Height: 5-1/2 in

	1108111.		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
3 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			