PROGRESS LIGHTING DESIGN**+SERIES**™

Project:			
Fixture Type:			
Location:			
Contact:			

P400356-31M Rivera

Rivera Collection 5-Light Matte Black Luxe Industrial Linear Light

Category: Island/Linear Finish: Matte Black (Painted) Construction: Steel Housing Glass/Shade: Clear textured Glass Flat Square/Rectangular



Width: 51-1/4 in Depth: 14-1/4 in Height: 8 in Overall Ht. W/Chain And Stem: 70 in

Clear textured Glass Flat Square/Rectangular Width: 10-5/8 in Height: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(5) Medium Base (E26) Socket	cULus Dry Location Listed
	120 VAC	Lamp Type	1-year Limited Warranty
1/8 IP mounting plate for outlet box included		Incandescent: 60-watt MAX per socket	
		LED: 12.5-watt MAX per socket	
3 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.	
Two 6", eight 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 15.75" W., 0.75" ht., 4.5" depth			