

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400358-205 Lusail

Lusail Collection Six-Light Soft Gold Luxe Industrial Chandelier

**Category:** Chandeliers  
**Finish:** Soft Gold (Painted) with Foundry Gold accent  
**Construction:** Steel Housing



Diameter: 32 in  
Height: 26 in  
Overall Ht. W/Chain And Stem: 88-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			