PROGRESS LIGHTING DESIGN**+SERIES**™

Project:	 	
Fixture Type:	 	
Location:		

Contact:

P400359-176 Laurel

Laurel Collection Six-Light Gilded Silver Transitional Chandelier

Category: Chandeliers Finish: Gilded Silver (Hand Painted) Construction: Steel Housing

recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth



Diameter: 28 in Height: 25-1/2 in Overall Ht. W/Chain And Stem: 87-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
	120 VAC	Lamp Type	1-year Limited Warranty
1/8 IP mounting plate for outlet box included		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
4 in of 9 Gauge chain supplied			
with quick link		Fully dimmable with dimmable bulbs.	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4"			