

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400359-204 Laurel

Laurel Collection Six-Light Gold Ombre Transitional Chandelier

Category: Chandeliers
Finish: Gold Ombre (Hand Painted)
Construction: Steel Housing



Diameter: 28 in
Height: 25-1/2 in
Overall Ht. W/Chain And Stem: 87-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
4 in of 9 Gauge chain supplied with quick link		Dimmable to 10% brightness (See Dimming Notes)	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.81" ht., 5.12" depth			