

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400361-176 Laurel



Laurel Collection 7-Light Gilded Silver Transitional Linear Light

Category: Island/Linear
Finish: Gilded Silver (Hand Painted)
Construction: Steel Housing

Length: 50-1/2 in
 Width: 16 in
 Height: 9-1/2 in
 Overall Ht. W/Stem And Swivel: 65-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(7) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Two 6", eight 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 11.81" W., 0.81" ht., 4.75" depth			