

Project:

Fixture Type:

Location:

Contact:

P400361-204 Laurel

Laurel Collection 7-Light Gold Ombre Transitional Linear Light

Category: Island/Linear

Finish: Gold Ombre (Hand Painted) **Construction:** Steel Housing



Length: 50-1/2 in Width: 16 in Height: 9-1/2 in

Overall Ht. W/Stem And Swivel: 65-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(7) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Two 6", eight 12" lengths of stem included		LED: 12.5-watt MAX per socket	
		Dimmable to 10% brightness (See	
Canopy covers a standard 4" recessed outlet box: 11.81" W., 0.81" ht., 4.75" depth		Dimming Notes)	