

Project:

Fixture Type:

Location:

Contact:

P400363-31M Rivera

Rivera Collection 5-Light Matte Black Luxe Industrial Chandelier

Category: Chandeliers
Finish: Matte Black (Painted)
Construction: Steel Housing

Glass/Shade: Clear textured Glass Flat Square/Rectangular



Diameter: 30 in Height: 16-3/4 in

Overall Ht. W/Chain And Stem: 79 in

Clear textured Glass Flat Square/Rectangular

Width: 3-5/8 in Height: 8-1/2 in

		Height. 6-1/2 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem Hung with 6 links of chain	10 feet of wire supplied	(5) Candelabra Base (E12) Socket	cULus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
3 in of 9 Gauge chain supplied with quick link		Fully dimmable with dimmable bulbs.	
One 6", four 12" lengths of stem included			
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			