

Project:
Fixture Type:
Location:

P400364-204

Loretta Collection Six-Light Gold Ombre Transitional Chandelier

Category: Chandeliers

Contact:

Loretta

Finish: Gold Ombre (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Glass Round



Diameter: 27 in Height: 20-1/2 in

Overall Ht. W/Chain: 72-1/2 in

Clear Glass Round Width: 5-7/16 in Height: 1 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
48 in of 9 Gauge square profile chain supplied with quick link		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.18" ht., 5.12" depth		bulbs.	