

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P400365-204 Loretta

Loretta Collection 28.25 in. Nine-Light Gold Ombre Transitional Chandelier

**Category:** Chandeliers  
**Finish:** Gold Ombre (Hand Painted)  
**Construction:** Steel Housing  
**Glass/Shade:** Clear Glass Round



Diameter: 36 in  
Height: 28-1/4 in  
Overall Ht. W/Chain: 122 in

Clear Glass Round  
Width: 6-5/16 in  
Height: 1-1/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(9) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
90 in of 9 Gauge square profile chain supplied with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 1.18" ht., 5.12" depth			