

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P400367-204 Chevall

Chevall Collection Six-Light Gold Ombre Modern Organic Chandelier

Category: Chandeliers
Finish: Gold Ombre (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Diameter: 24-7/8 in
 Height: 16-3/8 in
 Overall Ht. W/Chain: 67-1/2 in

Clear Pressed Glass Flat Square/Rectangular
 Width: 2-3/4 in
 Height: 5-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	10 feet of wire supplied	(6) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/4 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
48 in of 9 Gauge square profile chain supplied with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			