

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400368-176 Chevall

Chevall Collection Nine-Light Gilded Silver Modern Organic Chandelier

Category: Chandeliers
Finish: Gilded Silver (Hand Painted)
Construction: Steel Housing
Glass/Shade: Clear Pressed Glass Flat Square/Rectangular



Diameter: 32 in
Height: 23-1/2 in
Overall Ht. W/Chain: 117-1/2 in

Clear Pressed Glass Flat Square/Rectangular
Width: 2-3/4 in
Height: 5-15/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Chain	15 feet of wire supplied	(9) Candelabra Base (E12) Socket	cETLus Dry Location Listed
1/4 IP mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
90 in of 9 Gauge square profile chain supplied with quick link		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			
Weight of fixture exceeds NEC limits for outlet box hanging. Consult professional electrician for proper installation.			