

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P400370-009 Boundary

Boundary Collection Four-Light Brushed Nickel Grey Washed Oak Modern Chandelier

Category: Chandeliers

Finish: Brushed Nickel (Plated) with Grey Washed Oak accent

Construction: Steel Housing, Solid Wood accent



Diameter: 30 in
Height: 14-1/4 in
Overall Ht. W/Stem And Swivel: 70-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Medium Base (E26) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth			