

Project:
Fixture Type:
Location:
Contact:

P400370-31M Boundary

Boundary Collection Four-Light Matte Black Roasted Chicory Modern Chandelier

Category: Chandeliers

Finish: Matte Black (Hand Painted) with Roasted Chicory accent

Construction: Steel Housing, Solid Wood accent



Diameter: 30 in Height: 14-1/4 in

Overall Ht. W/Stem And Swivel: 70-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling Stem	10 feet of wire supplied	(4) Medium Base (E26) Socket	cETLus Dry Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
One 6", four 12" lengths of stem included		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable	
Canopy covers a standard 4" recessed outlet box: 5.12" W., 0.75" ht., 5.12" depth		bulbs.	